

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

50X EO M Plan Apo Long working Distance Infinity Corrected



50XEOMPlan Apo Long Working Distance Infinity Corrected, #59-879

Stock #59-879 [CONTACT US](#)

- 1 + €2.735,00

ADD TO CART

Qty 1+

€2.735,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View (mm):
0.48

Horizontal Field of View, 1/2" Sensor:
0.128mm

Horizontal Field of View, 2/3" Sensor:
0.176mm

Horizontal Field of View, 1" Sensor:
0.256mm

Focal Length FL (mm):

4.00
Length (mm): 82.00
Length excluding Threads (mm): 82.00
Magnification: 50X
Maximum Diameter (mm): 34
Numerical Aperture NA: 0.55
Mounting Threads: M26 x36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 0.5
Depth of Field (µm): 0.90
Field of View, 24 Diameter Field Eyepiece (mm): 0.48
Operating Temperature (°C): +10 to +40
Operating Humidity: <85% with no condensation
Working Distance (mm): 13.0
Weight (g): 320
Wavelength Range (nm): 390 - 780
Style: Infinity Corrected
Field Number (mm): 24
Parfocal Length (mm): 95
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View