

TECHSPEC®

50mm Dia., 0.83 Numerical Aperture, 900-1700nm Coated, Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock #17-012 3-4 DAYS

[Other Coating Options](#)



1



€790,00

ADD TO CART

Qty 1-5

€790,00

Qty 6+

€632,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.00 +0.00/-0.025

Effective Focal Length EFL (mm):
30.00 @ 587.6nm

Numerical Aperture NA:

0.83
Back Focal Length BFL (mm): 18.06
Substrate: N-SF6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: SWIR+ (900-1700nm)
Coating Specification: Ravg <0.5% @ 900 - 1700nm @ ±30° AOI Rabs <1.5% @ 900 - 1700nm @ ±30° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 45.00
Edge Thickness ET (mm): 7.35
Center Thickness CT (mm): 21.56 ±0.10
f/#: 0.60
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 900 - 1700
Conjugate Distance: Infinite
Power (diopters): 33.33

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant