

TECHSPEC® 5.0mm Dia. x 12.0mm FL, VIS 0° Coated, Plano-Convex Lens



Stock **#47-870** ☐ In Stock
[Other Coating Options](#)

1 **€46,00**

ADD TO CART

Qty 1-9
€46,00
Qty 10+
€41,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
5.00 +0.0/-0.025

Effective Focal Length EFL (mm):

12.00 @ 587.6nm
Back Focal Length BFL (mm): 10.83
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.77 ±0.05
Edge Thickness ET (mm): 1.25
Radius R₁ (mm): 6.22
Clear Aperture CA (mm): 4.5
f/#: 2.4
Numerical Aperture NA: 0.21
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, Reference: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant