

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 50mm Dia. X 200mm FL, NIR II Coated, Achromatic Lens



Stock #47-319 ☐ In Stock

-

1

+

€267,00

ADD TO CART

Qty 1-5

€267,00

Qty 6+

€213,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.025

Effective Focal Length EFL (mm):
200.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 191.15
Focal Length Specification Wavelength (nm) : 880.00
Clear Aperture CA (mm) : 49.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 14.50 ±0.20
Center Thickness CT 1 (mm) : 9.00 ±0.10
Center Thickness CT 2 (mm) : 5.50 ±0.10
Radius R₁ (mm) : 114.74
Radius R₂ (mm) : -114.74
Radius R₃ (mm) : -1258.40
Edge Thickness ET (mm) : 11.49
Substrate : N-LAK22 / N-SF6
Surface Quality : 40-20
f/# : 4.00
Numerical Aperture NA : 0.13
Coating : NIR II (750-1550nm)
Coating Specification : R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 750 - 1550

Regulatory Compliance

RoHS 2015 : Compliant
Reach 224 : Compliant
Certificate of Conformance : View