

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 514.5nm CWL, 12.5mm Dia, 2nm Bandwidth, OD 6 Laser Line Bandpass Filter



Stock #68-938 ☐ In Stock

[Additional Bandwidths](#)



1



€332,00

ADD TO CART

Qty 1-9

€332,00

Qty 10+

€292,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50

Angle of Incidence (°):
0 ±2

Bandwidth (nm):

2.00
OD 5 Blocking Wavelength Range (nm) : 434.1 - 509.4 & 519.6 - 669.5
OD 6 Blocking Wavelength Range (nm): 473.3 - 506.8 & 522.2 - 566
Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): 8.5
Center Wavelength CWL (nm): 514.50
Design Wavelength DWL (nm): 514.5
Full Width-Half Max FWHM (nm): 3.60
Substrate: ☐ Fused Silica (Corning 7980)
Coating: Hard Coated
Surface Quality: 60-40
Thickness Tolerance (mm): +0.0/-0.1
Transmission (%): ≥90
Type: Bandpass Filter
Durability: Environmental: MIL-STD-810F, sect. 507.4 Durability: MIL-C-48497A, sect. 3.4.1
Transmitted Wavefront, RMS: <i>M4</i> @ 633nm
Mount Thickness (mm): 3.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View