

TECHSPEC®

50mm Dia. x 250mm FL VIS-EXT Coated, Double-Convex Lens



Stock **#89-204** 3-4 DAYS

[Other Coating Options](#)

-

1

+

€72,50

ADD TO CART

Qty 1-9
€72,50
Qty 10+
€65,25
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.00 +0.000/-0.025

Back Focal Length BFL (mm):
248.37

Effective Focal Length EFL (mm): 250.00
Coating: VIS-EXT (350-700nm)
Coating Specification: Ravg <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 4.93
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.5
Radius R₁=R₂ (mm): 257.57
Clear Aperture CA (mm): 49.00
f/#: 5.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.10
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
