

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 50mm Dia X -25mm FL, Enhanced Aluminum, Convex Mirror



Convex Mirrors

Stock #87-672 [CONTACT US](#)



1



€70,50

ADD TO CART

Qty 1-5

€70,50

Qty 6+

€56,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
50.00

Focal Length FL (mm):  
-25.00

Center Thickness CT (mm):  
8.00

|                                                                       |
|-----------------------------------------------------------------------|
| <b>Clear Aperture (%)</b> :<br>90.00                                  |
| <b>Coating</b> :<br>Enhanced Aluminum (450-650nm)                     |
| <b>Coating Specification</b> :<br>R <sub>avg</sub> >95% @ 450 - 650nm |
| <b>Coating Type</b> :<br>Metal                                        |
| <b>Dimensional Tolerance (mm)</b> :<br>+0.0/-0.1                      |
| <b>Edge Thickness ET (mm)</b> :<br>1.30                               |
| <b>Focal Length Tolerance (%)</b> :<br>±2                             |
| <b>Radius R (mm)</b> :<br>50.0                                        |
| <b>Substrate</b> : <input type="checkbox"/><br><a href="#">N-BK7</a>  |
| <b>Surface Accuracy</b> :<br>λ/2                                      |
| <b>Surface Quality</b> :<br>60-40                                     |
| <b>Thickness Tolerance (mm)</b> :<br>±0.1                             |
| <b>Type</b> :<br>Spherical Mirror                                     |
| <b>Wavelength Range (nm)</b> :<br>450 - 650                           |

### Regulatory Compliance

|                                                             |
|-------------------------------------------------------------|
| <b>RoHS 2015</b> :<br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance</b> :<br><a href="#">View</a> |
| <b>Reach 235</b> :<br><a href="#">Compliant</a>             |