

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 5.0mm Diameter X 30.0mm FL, 633nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex (PCX) Lenses



Stock #89-003 3-4 DAYS

[Other Coating Options](#)

1

€53,50

ADD TO CART

Qty 1-9

€53,50

Qty 10+

€48,25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
5.00 +0.0/-0.025

Effective Focal Length EFL (mm): 30.00 @ 587.6nm
Back Focal Length BFL (mm): 28.95
Coating: Laser V-Coat (633nm)
Coating Specification: R _{abs} <0.25% @ 633nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.60 ±0.05
Edge Thickness ET (mm): 1.40
Radius R₁ (mm): 15.50
Clear Aperture CA (mm): 4.5
f/#: 6.00
Numerical Aperture NA: 0.08
Design Wavelength DWL (nm): 633
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Damage Threshold, By Design: ☐ 5 J/cm ² @ 633nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant