

515/1030nm, 0.38 NA, foXXus Multi-Focus Objective | foXXus_0.07_0.22_NA0.38_515/1030

See More by [AdlOptica](#)



AdlOptica foXXus Multi-Focus Objectives

Stock #19-498 3-4 DAYS

- 1 + **€8.823,00**

ADD TO CART

Qty 1+

€8.823,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
12.9

Design Wavelength DWL (nm):
515, 1030

Diameter (mm):
34.00

Focal Length FL (mm):
17.00

Model Number: foXXus_0.07_0.22_NA0.38_515/1030
Length (mm): 39.00
Mount: C-Mount
Numerical Aperture NA: 0.38
Type: Objective
Working Distance (mm): 9.7 (8.7 with Protective Window)
Field of View (°): ±1
Note: Includes foXXus objective, mounted protective window (#19-501), and spanner wrench (#19-503)
Damage Threshold, By Design: ☐ 25 mJ @ 5ns
Beam Diameter (mm): 12.9 (maximum)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant