

# 5° Diffusing Angle 12.5mm Unmounted



Stock **#35-862** 3-4 DAYS

-

1

+

€90,00

ADD TO CART

|         |
|---------|
| Qty 1-5 |
| €90,00  |

|        |
|--------|
| Qty 6+ |
| €67,50 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

## Get Product Downloads

Angle Tolerance (°):  
±1

Diffusing Angle (°):  
5 (FWHM)

Diameter (mm):  
12.50

Dimensional Tolerance (mm):

|                                                                                                                 |
|-----------------------------------------------------------------------------------------------------------------|
| ±0.5                                                                                                            |
| <b>Operating Temperature (°C):</b><br>-30 to +100 (Maximum of 240 Hours)                                        |
| <b>Substrate:</b> <input type="checkbox"/><br>Polycarbonate                                                     |
| <b>Thickness (mm):</b><br>0.78                                                                                  |
| <b>Transmission (%):</b><br>>85                                                                                 |
| <b>Type:</b><br>Holographic Diffuser                                                                            |
| <b>Wavelength Range (nm):</b><br>400 - 700                                                                      |
| <b>Construction:</b><br>Unmounted                                                                               |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>0.22 J/cm <sup>2</sup> @ 1064nm, 10ns (typical) |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |