

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #17-588 3-4 DAYS



1



€150,00

ADD TO CART

Qty 1-5

€150,00

Qty 6+

€120,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Clear Aperture CA (mm):
22.86

Coating:
Dual-Band (532, 1064nm)

Coating Specification: R_{abs} <0.25% @ 532nm, R_{abs} <0.10% @ 1064nm
Diameter (mm): 25.40 +0.00/-0.10
Thickness (mm): 6.35 ±0.20
Design Wavelength DWL (nm): 532, 1064
Parallelism (arcmin): <3
Substrate: Fused Silica (Coming 7980)
Fused Silica Grade: 7980 0F
Surface Flatness (P-V): λ/10
Surface Quality: 10-5
Type: Laser Line Window
Edges: Fine Ground
Damage Threshold, By Design: □ 5J/cm² @ 532nm, 20ns, 20Hz, 15J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View