


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



5mm Aperture, Protected Silver, Compact 506 Dual Axis Galvanometer Scanner



Stock #16-037 3-4 DAYS



1



€2.800,00

ADD TO CART

Qty 1+

€2.800,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Mirror Aperture (mm):
5

Surface Flatness (P-V):
≤λ/4 @ 632.8nm

Type:
Dual Axis

Coating: Protected Silver
Scan Angle (°): 40 (Optical)
Substrate:  Silicon (Si)
Operating Temperature (°C): 0 to +50
Dimensions (mm): 36.7 x 29.2 x 40.2 (of mount. Galvos protrude ~17mm)
Power Requirement: ±24 VDC
Position Signal (V): ±10
Current - Peak (A): Maximum: 10
Current - RMS (A): 1.85 (Case @ 50°C)
Coil Resistance (Ω): 1.8
Rotor Inertia (gm-cm²): 0.014
Torque Constant (dyne-cm/A): 18,400
Coil Inductance (μH): 280
Back EMF Voltage (μV/°/s): 32.1
Step Response 0.1° (μs): 200
Model Number: ScannerMAX Compact 506
Power Supply: 1 x #16-045 Europe (CE Marked): 2 x #14-571

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View