

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

5X ZEISS EC Epiplan Objective

See More by [ZEISS](#)



ZEISS EC Epiplan Objectives



Stock #13-822 3-4 DAYS



1



€630,00

ADD TO CART

Qty 1+

€630,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Field of View (mm):
4.6

Focal Length FL (mm):
33.00

Model Number: 422030-9902-000
Length excluding Threads (mm): 33.20
Magnification: 5X
Maximum Diameter (mm): 30
Numerical Aperture NA: 0.13
Mounting Threads: M27 x0.75
Compatible Tube Lens Focal Length (mm): Focal Length: 164.50mm
Type: Microscope Objective
Typical Applications: Fluorescence, BrightField, Differential Interference Contrast, Reflected Light DIC, DIC with circular polarized light
Resolving Power (µm): 2.1
Depth of Field (µm): 16.30
Operating Temperature (°C): +10 to +40
Operating Humidity: 75% at 35°C
Working Distance (mm): 11.8
Weight (g): 130
Wavelength Range (nm): 480 - 650
Style: Infinity Corrected
Manufacturer: ZEISS
Field Number (mm): 23
Parfocal Length (mm): 45
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View