

TECHSPEC® 6.35mm Dia. 532nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#38-890** 3-4 DAYS



1



€132,00

ADD TO CART

Qty 1-5

€132,00

Qty 6+

€116,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%) 85
Back Surface: Commercial Polish
Reflection at DWL (%) 99.8
Coating Specification: R_{abs} ≥99.8% @ 532nm
Wavelength Range (nm): 523 - 537
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (532nm)
Design Wavelength DWL (nm): 532
Diameter (mm): 6.35 +0.00/-0.10
Thickness (mm): 4.00 ±0.2
Angle of Incidence (°): 0-45
Substrate: □ Fused Silica (Corning 7980)
Damage Threshold, Reference: □ 10 J/cm² @ 532nm, 20ns, 20Hz

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View