

TECHSPEC® 6.0mm Dia. x 21.0mm FL, VIS-EXT Coated Plano-Convex Lens



Stock **#88-643** ☐ In Stock
[Other Coating Options](#)

1 **€39,50**

ADD TO CART

Qty 1-9
€39,50
Qty 10+
€35,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):

21.00 @ 587.6nm
Back Focal Length BFL (mm): 20.06
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.42 ±0.05
Edge Thickness ET (mm): 1.00
Radius R₁ (mm): 10.85
Clear Aperture CA (mm): 5.4
f/#: 3.5
Numerical Aperture NA: 0.14
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 700
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant