


TECHSPEC® 5mm Dia x 20mm FL VIS 0° Coated, UV Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#89-425** 3-4 DAYS

⊖ 1 ⊕

€125,00

ADD TO CART

Qty 1-5

€125,00

Qty 6+

€100,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
5.00 +0.0/-0.025

Effective Focal Length EFL (mm):

20.00 @ 587.6nm
Back Focal Length BFL (mm): 18.97
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate:  Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.50 ±0.05
Edge Thickness ET (mm): 1.15
Radius R₁ (mm): 9.17
Clear Aperture CA (mm): 4.5
f/#: 4
Numerical Aperture NA: 0.125
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, Reference:  5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant