

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 632.8nm, 12.5mm Diameter, Raman Edge Filter



Stock #86-226 3-4 DAYS



1



€505,00

ADD TO CART

Qty 1-9

€505,00

Qty 10+

€420,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.1

Angle of Incidence (°):
0 ±2

Optical Density OD (Average):
≥6.0

Cut-On Wavelength (nm): 639.10
Design Wavelength DWL (nm): 632.8
Substrate:  Fused Silica (Corning 7980)
Coating: Hard Coated
Rejection Wavelength (nm): 513 - 632.8
Surface Quality: 60-40
Thickness Tolerance (mm): +0.1/-0.1
Transmission (%): >93
Type: Longpass Filter
Transition Width (nm): <6.3
Clear Aperture (%): >80
Durability: Environmental: MIL-STD-810F Physical: MIL-C-48497A
Transmitted Wavefront, RMS: <λ/4 @ 633nm
Mount Thickness (mm): 3.5
Note: Bandwidth (nm): >750
Coating Specification: T _{avg} ≥93% @ 641.0 - 1427.4nm
Wavelength Range (nm): 513 - 1427
Laser Blocking Wavelength (nm): 632.8

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View