

6.35mm Dia., 0.5mm Thick, 400-1100nm, High Durability AR Coated Sapphire Window



High Durability Anti-Reflection (AR) Coated Sapphire Windows

Stock #18-462 3-4 DAYS



1



€102,50

ADD TO CART

Qty 1-10

€102,50

Qty 11+

€92,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
72.24

Axis Orientation:
Random

Bevel:
Protective as needed

Birefringence (n_o-n_e): 0.008 for Visible Light Orthogonal to Optical Axis
Clear Aperture (%): 90
Clear Aperture CA (mm): 5.72
Diameter (mm): 6.35 ±0.05
Thickness (mm): 0.50 ±0.05
Coating: Hardened VIS-NIR (400-1100nm)
Coating Specification: R _{avg} <1.5% @ 400 - 1100nm R _{abs} <2.0% @ 400 - 1100nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 8.8
Density (g/cm³): 3.97
Edges: Fine Ground
Index of Refraction n_d: 1.77
Knoop Hardness (kg/mm²): 1900
Parallelism (arcmin): ≤3.5
Poisson's Ratio: 0.27
Substrate: Sapphire (Al ₂ O ₃)
Surface Flatness (P-V): 2λ (typical)
Surface Quality: 80-50
Type: Protective Window
Wavelength Range (nm): 400 - 1100
Young's Modulus (GPa): 435
Coating Abrasion: Severe, per MIL-C-675C Paragraph 4.5.10
Coating Adhesion: Per MIL-M-13508C Paragraph 4.4.6
Coating Humidity: ≥24 Hours per MIL-C-675C paragraph 4.5.8
Coating Salt Solubility: ≥24 Hours Immersion per MIL-C-675C paragraph 4.5.7
Coating Salt Spray: ≥24 Hours per MIL-C-675C paragraph 4.5.9
Coating Temperature (°F): -80 to +160 per MIL-M-13508C Paragraph 4.4.4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View