

In order to provide more accurate inventory information, please select your shipping country:


Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 6.0mm Dia. X 7.5mm FL, YAG-BBAR Coated Plano-Convex Lens



YAG-BBAR Coated Plano-Convex (PCX) Lenses



Stock #88-797 3-4 DAYS

[Other Coating Options](#)

1

€40,50

ADD TO CART

Qty 1-9

€40,50

Qty 10+

€36,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm): 7.50 @ 587.6nm
Back Focal Length BFL (mm): 6.10
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 2.50 ±0.05
Edge Thickness ET (mm): 1.68
Radius R₁ (mm): 5.89
Clear Aperture CA (mm): 5.4
f/#: 1.25
Numerical Aperture NA: 0.40
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 532 - 1100
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant