

6mm Dia. x 18mm FL, Small Diameter Plastic Aspheric Lens



Stock #36-629 3-4 DAYS

- 1 + **€30,00**

ADD TO CART

Qty 1-10
€30,00
Qty 11+
€25,00
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 ±0.20

Effective Focal Length EFL (mm):
18.00 @ 550nm

Numerical Aperture NA: 0.17
Back Focal Length BFL (mm): 14.93
Substrate: ☐ Acrylic V825
Focal Length Tolerance (%): ±1.5
Aspheric Design Wavelength (nm): 550
Coating: Uncoated
Surface Quality: 60-40
Clear Aperture CA (mm): 5
Edge Thickness ET (mm): 3.50
Center Thickness CT (mm): 4.00 ±0.20
f/#: 2.94
Bevel: Protective bevel as needed
Type: Aspheric Lens
Wavelength Range (nm): 400 - 1500
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View