


TECHSPEC® 6mm Dia. x 12mm FL, NIR II Coated, Achromatic Lens



Stock **#45-784** 3-4 DAYS

⊖ 1 ⊕ **€102,00**

ADD TO CART

Qty 1-5

€102,00

Qty 6+

€81,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):
12.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 9.30
Focal Length Specification Wavelength (nm) : 880.00
Clear Aperture CA (mm) : 5.4
Centering (arcmin) : <1
Center Thickness CT (mm) : 4.50 ±0.10
Center Thickness CT 1 (mm) : 3.20 ±0.05
Center Thickness CT 2 (mm) : 1.30 ±0.05
Radius R₁ (mm) : 6.84
Radius R₂ (mm) : -5.99
Radius R₃ (mm) : -69.82
Edge Thickness ET (mm) : 3.74
Substrate: ☐ N-LAK22 / N-SF6
Surface Quality : 40-20
f/# : 2
Numerical Aperture NA : 0.25
Coating : NIR II (750-1550nm)
Coating Specification : R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 750 - 1550

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View