

TECHSPEC® 6.35 x 6.35mm 266nm 45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#39-576** 3-4 DAYS



1



€126,00

ADD TO CART

Qty 1-5

€126,00

Qty 6+

€111,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%) : 85
Back Surface: Commercial Polish
Reflection at DWL (%) : 99.5
Coating Specification: R _{abs} >99.5% @ 266nm R _{avg} >99.5% @ 263 - 268nm
Wavelength Range (nm) : 263 - 268
Surface Flatness (P-V) : λ/10
Coating Type: Dielectric
Coating: Laser Mirror (263-268nm)
Design Wavelength DWL (nm) : 266
Dimensions (mm) : 6.35 x 6.35 +0.00/-0.10
Thickness (mm) : 3.18 ±0.20
Angle of Incidence (°) : 45
Substrate: ☐ Fused Silica (Corning 7980)
Damage Threshold, Reference: ☐ 2.5 J/cm ² @ 266nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View