

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 75mm Dia., 0.63 Numerical Aperture Uncoated, Aspheric Lens



Stock #14-994 3-4 DAYS

[Other Coating Options](#)



1



€740,00

ADD TO CART

Qty 1-5

€740,00

Qty 6+

€592,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
75.00 +0.0/-0.1

Effective Focal Length EFL (mm):
60.00 @ 587.6nm

Numerical Aperture NA:

0.63
Back Focal Length BFL (mm): 45.77
Substrate: ☐ N-SF5
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 67.5
Edge Thickness ET (mm): 4.73
Center Thickness CT (mm): 23.80 ±0.1
f/#: 0.80
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 380 - 2500
Conjugate Distance: Infinite
Power (diopters): 16.67

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View