

**TECHSPEC® 76.2 x 76.2mm EFL 90° Protected Aluminum 100Å Off-Axis Parabolic Mirror**



Stock **#35-522** ☒ In Stock

[Other Coating Options](#)



1



€705,00

ADD TO CART

|         |
|---------|
| Qty 1-5 |
| €705,00 |

|         |
|---------|
| Qty 6+  |
| €634,50 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:  
Off-Axis Parabolic Mirror

Diameter (mm):  
76.20 +0.00/-0.38

Effective Focal Length EFL (mm):

|                                                                                                                |
|----------------------------------------------------------------------------------------------------------------|
| 76.20                                                                                                          |
| <b>Focal Length Tolerance (%):</b><br>±1                                                                       |
| <b>Radius of Curvature (mm):</b><br>76.20                                                                      |
| <b>Coating:</b><br>Protected Aluminum (400-2000nm)                                                             |
| <b>Coating Type:</b><br>Metal                                                                                  |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≥85% @400 - 700nm<br>R <sub>avg</sub> ≥97% @2,000 - 12,000nm |
| <b>Off-Set Angle (°):</b><br>90                                                                                |
| <b>Parent Focal Length PFL (mm):</b><br>38.1                                                                   |
| <b>Surface Figure, RMS:</b><br>3/4λ                                                                            |
| <b>Surface Roughness (Angstroms):</b><br><100 RMS                                                              |
| <b>Wavelength Range (nm):</b><br>400 - 2000                                                                    |
| <b>Clear Aperture (%):</b><br>90                                                                               |
| <b>Surface Quality:</b><br>80-50                                                                               |
| <b>Compatible Mounting Plates:</b><br><a href="#">#63-375</a>                                                  |
| <b>Substrate:</b><br>Aluminum 6061-T6                                                                          |
| <b>Y Offset (mm):</b><br>76.2                                                                                  |
| <b>Reflected Wavefront, RMS:</b><br>3/2λ                                                                       |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |