

TECHSPEC® 785nm CWL, 25mm Dia, 3nm Bandwidth, OD 6 Laser Line Bandpass Filter



Stock **#68-978** [CONTACT US](#)

[Additional Bandwidths](#)



1



€665,00

ADD TO CART

Qty 1-9

€665,00

Qty 10+

€585,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Angle of Incidence (°):
0 ±2

Bandwidth (nm):

3.00
OD 5 Blocking Wavelength Range (nm) : 612 - 777 & 793 - 1214
OD 6 Blocking Wavelength Range (nm): 722 - 773 & 797 - 864
Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): 21.00
Center Wavelength CWL (nm): 785.00
Design Wavelength DWL (nm): 785
Full Width-Half Max FWHM (nm): 5.50
Substrate: ☐ Fused Silica (Corning 7980)
Coating: Hard Coated
Surface Quality: 60-40
Thickness Tolerance (mm): +0.0/-0.1
Transmission (%): ≥90
Type: Bandpass Filter
Durability: Environmental: MIL-STD-810F, sect. 507.4 Durability: MIL-C-48497A, sect. 3.4.1
Transmitted Wavefront, RMS: λ/4 @ 633nm
Mount Thickness (mm): 3.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View