

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 76.2 X 178.5mm EFL 45° Protected Aluminum 100A Off-Axis Parabolic Mirror



Stock #35-588 3-4 DAYS

[Other Coating Options](#)



1



€705,00

ADD TO CART

Qty 1-5

€705,00

Qty 6+

€634,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
76.20 +0.00/-0.38

Effective Focal Length EFL (mm):

178.53
Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 304.80
Coating: Protected Aluminum (400-2000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥85% @400 - 700nm R _{avg} ≥97% @2,000 - 12,000nm
Off-Set Angle (°): 45
Parent Focal Length PFL (mm): 152.4
Surface Figure, RMS: 3/4λ
Surface Roughness (Angstroms): <100 RMS
Wavelength Range (nm): 400 - 2000
Clear Aperture (%): 90
Surface Quality: 80-50
Compatible Mounting Plates: #63-375
Substrate: Aluminum 6061-T6
Y Offset (mm): 126.26
Reflected Wavefront, RMS: 3/2λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant