

TECHSPEC® 76.2 x 646mm EFL 15° Protected Gold 100Å Off-Axis Parabolic Mirror



Stock **#35-605** 3-4 DAYS

[Other Coating Options](#)



1



€835,00

ADD TO CART

Qty 1-5

€835,00

Qty 6+

€751,50

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
76.20 +0.00/-0.38

Effective Focal Length EFL (mm):

646.00
Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 1,270.00
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥94% @ 700 - 800nm R _{avg} ≥97% @ 800 - 2,000nm R _{avg} ≥98% @ 2,000 - 12,000nm
Off-Set Angle (°): 15
Parent Focal Length PFL (mm): 635.00
Surface Figure, RMS: 3/4λ
Surface Roughness (Angstroms): <100 RMS
Wavelength Range (nm): 700 - 10000
Clear Aperture (%): 90
Surface Quality: 80-50
Compatible Mounting Plates: #63-375
Substrate: Aluminum 6061-T6
Y Offset (mm): 167.2
Reflected Wavefront, RMS: 3/2λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant