

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 7X, UV-VIS Vega® Broadband Beam Expander



TECHSPEC® Vega™ Broadband Beam Expanders

Stock #39-732 3-4 DAYS



1



€572,00

ADD TO CART

Qty 1-9
€572,00

Qty 10+
€506,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Coating:
Laser UV-VIS (250-532nm)

Design Wavelength DWL (nm):
Broadband

Entrance Aperture (mm): 7.1
Exit Aperture (mm): 25.5
Expansion Power: 7X
Substrate: ☐ Fused Silica (Corning 7980)
Length (mm): 94.55
Mounting Threads: Input: Male M30 x 1 Output: Female M34 x 0.5
Transmission (%): >92.5 (nominal)
Type: Beam Expander
Weight (g): 170
Housing Diameter (mm): 39.95
Transmitted Wavefront, P-V: λ/10 for 2.6mm input beam (nominal, λ = DWL)
Coating Specification: R _{avg} ≤1.25% @ 250 - 532nm @ 0° AOI
Wavelength Range (nm): 250 - 532
Style: Fixed Magnification
Damage Threshold, By Design: ☐ 1 J/cm² @ 532nm, 20ns, 20Hz
Divergence Adjustment: Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View