

800nm, 0.80 NA, aplanoXX Aplan Objective | aplanoXX NA0.8_20_800

See More by [AdlOptica](#)



AdlOptica aplanoXX Aplan Objectives



Stock **#19-492** 3-4 DAYS

- 1 + **€8.135,00**

ADD TO CART

Qty 1+
€8.135,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
20

Design Wavelength DWL (nm):
800

Diameter (mm):
44.00

Focal Length FL (mm): 12.50
Model Number: aplanoXXNA0.8_20_800
Length (mm): 54.10
Mount: C-Mount
Numerical Aperture NA: 0.80
Type: Objective
Working Distance (mm): 2.5 (1.6 with Protective Window)
Field of View (°): ±0.3
Note: Includes aplanoXX objective, mounted protective window (#19-496), and spanner wrench #19-497
Wavelength Range (nm): 770 - 900
Damage Threshold, By Design: ☐ 100 mJ @ 5ns 300 μJ @ 1ps
Focusing Depth (mm): 0 - 4
Beam Diameter (mm): 20 (maximum)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant
