

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

8.5mm Dia. X 7.4mm FL, NIR I Coated, Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock #15-880 3-4 DAYS

[Other Coating Options](#)



1



€56,00

ADD TO CART

Qty 1-10

€56,00

Qty 11+

€49,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
8.50 +/-0.3

Effective Focal Length EFL (mm):
7.40 @ 587.6nm

Numerical Aperture NA:
0.57

Back Focal Length BFL (mm): 4.80
Substrate:  Liba2000+
Focal Length Tolerance (%): ±5
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Centering (arcmin): ≤25
Surface Quality: Molded Side: 5/3 x 0.4; E 0.2 Polished Side: 5/3 x 0.25; E 0.2
Clear Aperture CA (mm): 6.80
Edge Thickness ET (mm): 1.8
Center Thickness CT (mm): 4.00 ±0.20
f#: 0.87
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 8.5
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant