

In order to provide more accurate inventory information, please select your shipping country:


Select Your Country/Region: European Union



SUBMIT

8mm Dia., 0.5mm Thick, Coherent® Uncoated Polycrystalline CVD Diamond window

See More by [Coherent®](#)



Stock #12-667 3-4 DAYS



1



€900,00

ADD TO CART

Qty 1-10

€900,00

Qty 11+

€810,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Bevel:
Protective as needed

Clear Aperture (%):
≥90

Clear Aperture CA (mm):
7.20

Diameter (mm): 8.00 ±0.05
Thickness (mm): 0.50 ±0.10
Coating: Uncoated
Index of Refraction n_d: 2.38 @ 10.6μm
Parallelism (arcmin): <5
Substrate: Coherent® Optical Grade Polycrystalline CVD Diamond
Surface Quality: 40-20
Type: Protective Window
Wavelength Range (nm): 300 - 25000

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View