


8mm Square, 0.5mm Thick, Coherent® Uncoated Polycrystalline CVD Diamond Window

See More by [Coherent®](#)



Stock **#12-666** [CONTACT US](#)

- 1 + **€1.135,00**

ADD TO CART

Qty 1-10
€1.135,00

Qty 11+
€1.021,50

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Bevel:
Protective as needed

Clear Aperture (%):
≥90

Clear Aperture CA (mm):
7.20 x 7.20

Dimensions (mm): 8.00 x 8.00
Thickness (mm): 0.50 ±0.10
Coating: Uncoated
Index of Refraction n_d: 2.38 @ 10.6µm
Parallelism (arcmin): <5
Substrate: Coherent® Optical Grade Polycrystalline CVD Diamond
Surface Quality: 40-20
Type: Protective Window
Wavelength Range (nm): 300 - 25000
Length (mm): 8.00
Width (mm): 8.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View