

TECHSPEC® 8X, 532nm Scorpii® Nd:YAG Beam Expander



8X, 532nm LCht Fixed YAG Beam Expander, #37-065

Stock **#37-065** 3-4 DAYS



1



€184,00

ADD TO CART

Qty 1-9

€184,00

Qty 10+

€163,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Coating:
VIS 0° (425-675nm)

Design Wavelength DWL (nm):
532

Entrance Aperture (mm): 3.7
Exit Aperture (mm): 27
Expansion Power: 8X
Substrate: ☐ Optical Glass
Length (mm): 108.80
Mounting Threads: M22 x0.75
Transmission (%) : >98 (nominal)
Type: Beam Expander
Weight (g): 159
Housing Diameter (mm): 29.95/39.95
Transmitted Wavefront, P-V: <λ/4 @ 532nm for Input Beam ≤1.7mm (by design)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Wavelength Range (nm): 532
Style: Fixed Magnification
Divergence Adjustment: None

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View