

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 8° Nom. 12.5mm Dia. VIS 0°, N-BK7 wedge Prism



Stock #35-790 □ In Stock



1



€47,50

ADD TO CART

Qty 1-5

€47,50

Qty 6+

€38,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
VIS 0° (425-675nm)

Angle Tolerance (arcsec):
±30

Bevel:
Protective bevel as needed

Coating Specification: R_{avg} ≤0.4% @ 425 - 675nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1
Design Wavelength DWL (nm): 632.8
Diameter (mm): 12.50 +0.00/-0.10
Edge Thickness ET (mm): 1.5
Image Orientation: Beam Deviation
Power (diopters): 14.05
Ray Deviation @ 633nm (°): 8.00
Substrate: N-BK7
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 1.50
Type: Wedge Prism
Wavelength Range (nm): 425 - 675
Wedge Angle: 14° 51'

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant