

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 980nm CWL, 12.5mm Dia, 3.7nm Bandwidth, OD 6 Laser Line Bandpass Filter



Stock #68-952 ☐ In Stock

[Additional Bandwidths](#)



1



€332,00

ADD TO CART

Qty 1-9

€332,00

Qty 10+

€292,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
12.50

Angle of Incidence (°):  
0 ±2

Bandwidth (nm):

|                                                                                                         |
|---------------------------------------------------------------------------------------------------------|
| 3.7                                                                                                     |
| <b>OD 5 Blocking Wavelength Range (nm) :</b><br>724.4 - 970.2 & 989.8 - 1332.6                          |
| <b>OD 6 Blocking Wavelength Range (nm):</b><br>901.6 - 965.3 & 994.7 - 1078                             |
| <b>Optical Density OD (Average):</b><br>≥6.0                                                            |
| <b>Clear Aperture CA (mm):</b><br>8.5                                                                   |
| <b>Center Wavelength CWL (nm):</b><br>980.00                                                            |
| <b>Design Wavelength DWL (nm):</b><br>980                                                               |
| <b>Full Width-Half Max FWHM (nm):</b><br>6.90                                                           |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Fused Silica</a> (Corning 7980)               |
| <b>Coating:</b><br>Hard Coated                                                                          |
| <b>Surface Quality:</b><br>60-40                                                                        |
| <b>Thickness Tolerance (mm):</b><br>+0.0/-0.1                                                           |
| <b>Transmission (%):</b><br>≥90                                                                         |
| <b>Type:</b><br>Bandpass Filter                                                                         |
| <b>Durability:</b><br>Environmental: MIL-STD-810F, sect. 507.4<br>Durability: MIL-C-48497A, sect. 3.4.1 |
| <b>Transmitted Wavefront, RMS:</b><br><i>M4</i> @ 633nm                                                 |
| <b>Mount Thickness (mm):</b><br>3.5                                                                     |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 209:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |