

TECHSPEC® 9mm Dia. x 27mm EFL, UV-VIS Coated, Near UV Achromatic Lens



Stock **#35-994** 3-4 DAYS

⊖ 1 ⊕ **€134,00**

ADD TO CART

Qty 1-5

€134,00

Qty 6+

€107,25

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm):
27.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 24.13
Focal Length Specification Wavelength (nm) : 405.00
Clear Aperture CA (mm) : 8.1
Centering (arcmin) : <1
Center Thickness CT (mm) : 5.25 ±0.10
Center Thickness CT 1 (mm) : 3.75 ±0.05
Center Thickness CT 2 (mm) : 1.50 ±0.05
Radius R₁ (mm) : 14.60
Radius R₂ (mm) : -12.12
Radius R₃ (mm) : -40.64
Edge Thickness ET (mm) : 4.29
Substrate : ☐ N-FK5 / F2H1
Surface Quality : 40-20
f/# : 3
Numerical Aperture NA : 0.17
Coating : UV-VIS (345-700nm)
Coating Specification : R _{avg} ≤1.5% @ 345 - 700nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 345 - 700

Regulatory Compliance

RoHS 2015 : Exempt
Certificate of Conformance : View
Reach 235 : Compliant