

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union


SUBMIT

# Allied Vision Alvium 1800 U-500C, 1/2.5" 5.0MP S-Mount, USB 3.1 Color Camera (Partial Housing)

See More by [Allied Vision](#)



Allied Vision Alvium Camera, Partial Housing, S-Mbunt (Front)



Stock #14-143 [CONTACT US](#)

[Similar Cameras](#)

1 **€315,00**

ADD TO CART

Qty 1+

€315,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:  
USB 3.1 Gen 1

|                                                                                             |
|---------------------------------------------------------------------------------------------|
| <b>Type:</b><br>Color Camera                                                                |
| <b>Manufacturer:</b><br>Allied Vision                                                       |
| <b>Mounting Threads:</b><br>1/4-20 and M6 with Tripod Mount Adapter <a href="#">#14-156</a> |
| <b>Image Buffer:</b><br>256KB                                                               |
| <b>Camera Family:</b><br>Alvium                                                             |
| <b>Model Number:</b><br>1800 U-500c                                                         |
| <b>Imaging Sensor:</b><br>ON Semi AR0521                                                    |
| <b>Type of Sensor:</b><br>Progressive Scan CMOS                                             |
| <b>Type of Shutter:</b><br>Rolling                                                          |
| <b>Camera Sensor Format:</b><br>1/2.5"                                                      |
| <b>Resolution (MegaPixels):</b><br>5.00                                                     |
| <b>Pixels (H x V):</b><br>2,592 x 1,944                                                     |
| <b>Pixel Size, H x V (µm):</b><br>2.2 x 2.2                                                 |
| <b>Sensing Area, H x V (mm):</b><br>5.7 x 4.3                                               |
| <b>Frame Rate (fps):</b><br>67.00                                                           |
| <b>Pixel Depth:</b><br>8/10 bit                                                             |
| <b>Exposure Time:</b><br>13µs - 849ms                                                       |
| <b>Connector:</b><br>USB 3.1 Gen 1, Micro-B                                                 |
| <b>Power Supply:</b><br>Power over USB or via GPIO                                          |
| <b>Power Consumption (W):</b><br>2.2                                                        |
| <b>GPIOs:</b><br>4 Programmable TTL GPIOs                                                   |
| <b>Synchronization:</b><br>Hardware Trigger (GPIO) or Software Trigger                      |
| <b>Dimensions (mm):</b><br>25 x 29 x 29 (includes connectors and lens mount)                |
| <b>Weight (g):</b><br>45                                                                    |
| <b>Mount:</b><br>M12 x 0.5 (S-Mbunt)                                                        |
| <b>Housing:</b><br>Partial                                                                  |
| <b>Interface Port Orientation:</b><br>Back Panel                                            |
| <b>Operating Temperature (°C):</b><br>-20 to +65 (housing temperature)                      |
| <b>Storage Temperature (°C):</b><br>-20 to +85                                              |
| <b>GPIO Connector Type:</b><br>7-pin JST                                                    |
| <b>Machine Vision Standard:</b><br>USB3 Vision v1.0, GenICam                                |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |