

[All Products](#) / [Cameras](#) / [USB Cameras](#) / [Allied Vision Alvium USB 3.1 Cameras](#)

[See all 141 Products in Family](#)

Allied Vision Alvium 1800 U-1236m, 1.1" 12.4MP C-Mount, USB 3.1 Monochrome Camera

See More by [Allied Vision](#)



Allied Vision Alvium Camera, Full Housing (Front)



Stock **#14-889** 3-4 DAYS

[Similar Cameras](#)



1



€1.974,00

ADD TO CART

Qty 1+

€1.974,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:

USB 3.1 Gen 1

Type:

Monochrome Camera

Manufacturer:

Allied Vision

Mounting Threads: ¼-20 and M6 with Tripod Mount Adapter #14-156
Image Buffer: 256KB
Camera Family: Alvium
Model Number: 1800 U-1236m
Imaging Sensor: Sony IMX304
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1.1"
Resolution (MegaPixels): 12.40
Pixels (H x V): 4,112 x 3,008
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 14.2 x 10.4
Frame Rate (fps): 22.00
Pixel Depth: 8/10/12 bit
Exposure Time: 169µs - 10s
Connector: USB 3.1 Gen 1, Micro-B
Power Supply: Power over USB or via GPIO
Power Consumption (W): 2.9
GPIOs: 4 Programmable TTL GPIOs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 38 x 29 x 29 (includes connectors and lens mount)
Weight (g): 60
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 72
Operating Temperature (°C): -20 to +65 (housing temperature)
Storage Temperature (°C): -20 to +85
GPIO Connector Type: 7-pin JST
Machine Vision Standard: USB3 Vision v1.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant