

Allied Vision Prosilica GT5120 APS-H F-Mount Monochrome Camera

See More by [Allied Vision](#)



Stock **#14-738** [CONTACT US](#)

- 1 +

€7.645,00

ADD TO CART

Qty 1+
€7.645,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Monochrome Camera

Manufacturer:
Allied Vision

Mounting Threads:
1/4-20 with Tripod Mount Adapter [#87-412](#)

Image Buffer:
128MB

Camera Family: Prosilica GT
Model Number: GT 5120
Imaging Sensor: ON Semi PYTHON 25K
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: APS-H
Resolution (MegaPixels): 26.20
Pixels (H x V): 5,120 x 5,120
Pixel Size, H x V (µm): 4.5 x 4.5
Sensing Area, H x V (mm): 23.0 x 23.0
Frame Rate (fps): 4.59
Pixel Depth: 10 bit
Exposure Time: Auto Exposure
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power Supply Required and Sold Separately. USA: #15-281 Europe: #15-281 Japan: #15-281 China: #15-281
Power Consumption (W): 5.02 (12VDC External Power Supply) 6.3 (PoE)
GPIOs: 1 opto-isolated input, 2 opto-isolated outputs, 1 non-isolated input, 2 non-isolated outputs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 53.3 × 66 × 53.3 (excludes connectors and lens mount)
Weight (g): 372
Mount: F-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 50.7
Operating Temperature (°C): -20 to +65
Storage Temperature (°C): -20 to +70
GPIO Connector Type: 12-pin Hirose (HR10)
Machine Vision Standard: GigE Vision V1.2, GenICam SFNC V1.2.1

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant