

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

Basler ace2 azA1920-51gcBAS Color GigE Basic Camera



Basler ace2 GigE Cameras (Front)



Stock #16-594 [CONTACT US](#)

[Similar Cameras](#)



1



€379,00

ADD TO CART

Qty 1+

€379,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:  
GigE (PoE)

Type:  
Color Camera

Manufacturer:  
Basler

|                                                                                            |
|--------------------------------------------------------------------------------------------|
| <b>Mounting Threads:</b><br>¼-20 with Tripod Mount Adapter <a href="#">#16-641</a>         |
| <b>Image Buffer:</b><br>Not Specified                                                      |
| <b>Camera Family:</b><br>ace2                                                              |
| <b>Model Number:</b><br>a2A1920-51gcBAS                                                    |
| <b>Imaging Sensor:</b><br>Sony IMX392                                                      |
| <b>Type of Sensor:</b><br>Progressive Scan CMOS                                            |
| <b>Type of Shutter:</b><br>Global                                                          |
| <b>Camera Sensor Format:</b><br>1/2.3"                                                     |
| <b>Resolution (MegaPixels):</b><br>2.30                                                    |
| <b>Pixels (H x V):</b><br>1,920 x 1,200                                                    |
| <b>Pixel Size, H x V (µm):</b><br>3.45 x 3.45                                              |
| <b>Sensing Area, H x V (mm):</b><br>6.6 x 4.1                                              |
| <b>Frame Rate (fps):</b><br>51.00                                                          |
| <b>Pixel Depth:</b><br>8/10/12 bit                                                         |
| <b>Exposure Time:</b><br>Freely Programmable                                               |
| <b>Connector:</b><br>GigE, RJ45 with Screw Locks                                           |
| <b>Power Supply:</b><br>Power over Ethernet (PoE) or via GPIO with <a href="#">#16-644</a> |
| <b>Power Consumption (W):</b><br>3.6                                                       |
| <b>GPIOs:</b><br>1 opto-coupled input line, 2 general purpose I/O (GPIO) lines             |
| <b>Synchronization:</b><br>Hardware Trigger (GPIO), Software Trigger, or Free-Run          |
| <b>Dimensions (mm):</b><br>55.5 x 29 x 29 (excludes connectors and lens mount)             |
| <b>Weight (g):</b><br><100                                                                 |
| <b>Mount:</b><br>C-Mount                                                                   |
| <b>Housing:</b><br>Full                                                                    |
| <b>Interface Port Orientation:</b><br>Back Panel                                           |
| <b>Dynamic Range (dB):</b><br>Not Specified                                                |
| <b>Operating Temperature (°C):</b><br>-10 to +60                                           |
| <b>Storage Temperature (°C):</b><br>-20 to +80                                             |
| <b>GPIO Connector Type:</b><br>6-pin M8                                                    |
| <b>Machine Vision Standard:</b><br>GigE Vision 2.0, GenICam                                |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |