

Basler ace2 a2A5328-4gmBAS Monochrome GigE Basic Camera



Basler ace2 GigE Cameras (Front)



Stock **#16-603** [CONTACT US](#)

[Similar Cameras](#)



1



€2.359,00

ADD TO CART

Qty 1+

€2.359,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Monochrome Camera

Manufacturer:
Basler

Mounting Threads: ¼-20 with Tripod Mount Adapter #16-641
Image Buffer: Not Specified
Camera Family: ace2
Model Number: a2A5328-4gmBAS
Imaging Sensor: Sony IMX540
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1.2"
Resolution (MegaPixels): 24.40
Pixels (H x V): 5,328 x 4,608
Pixel Size, H x V (µm): 2.74 x 2.74
Sensing Area, H x V (mm): 14.6 x 12.6
Frame Rate (fps): 4.00
Pixel Depth: 8/10/12 bit
Exposure Time: Freely Programmable
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power over Ethernet (PoE) or via GPIO with #16-644
Power Consumption (W): 3.3
GPIOs: 1 opto-coupled input line, 2 general purpose I/O (GPIO) lines
Synchronization: Hardware Trigger (GPIO), Software Trigger, or Free-Run
Dimensions (mm): 55.5 x 29 x 29 (excludes connectors and lens mount)
Weight (g): <105
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 70.7
Operating Temperature (°C): -10 to +60
Storage Temperature (°C): -20 to +80
GPIO Connector Type: 6-pin M8
Machine Vision Standard: GigE Vision 2.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant