

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

Basler ace aca1600-60gc Color Gige Camera



Basler ace Gige Cameras



Stock #88-331 3-4 DAYS

[Similar Cameras](#)

- 1 +

€819,00

ADD TO CART

Qty 1+

€819,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Color Camera

Manufacturer: Basler
Mounting Threads: ¼-20 with Tripod Mount Adapter #88-517
Camera Family: ace
Model Number: acA1600-60gc
Imaging Sensor: e2v EV76C560
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global and Rolling
Camera Sensor Format: 1/1.8"
Resolution (MegaPixels): 2.00
Pixels (H x V): 1,600 x 1,200
Pixel Size, H x V (µm): 4.5 x 4.5
Sensing Area, H x V (mm): 7.2 x 5.4
Frame Rate (fps): 60.00
Pixel Depth: 12 bit
Exposure Time: Freely Programmable
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power Supply Required and Sold Separately. USA: #68-466 Europe: #68-466 Japan: #68-466 Korea: #68-466 China: #68-466
Power Consumption (W): 2.1 (12VDC External Power Supply) 2.7 (PoE)
GPIOs: 1 opto-coupled input line, 1 opto-coupled output line, 1 general purpose I/O (GPIO) line
Synchronization: Hardware Trigger (GPIO), Software Trigger, or Free-Run
Dimensions (mm): 42 x 29 x 29 (excludes connectors and lens mount)
Weight (g): 90
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): Not Specified
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -20 to +80
GPIO Connector Type: 6-pin Hirose (HR10)
Machine Vision Standard: GigE Vision
Operating System: Software Driver: Windows, Linux - 32 and 64 bit

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View

