

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

Basler boost CoaXPress 2.0 Color Camera Kit



Basler boost CoaXPress 2.0 Camera Kits

Stock #14-256 [CONTACT US](#)



1



€4.149,00

ADD TO CART

Qty 1+

€4.149,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:

CoaXPress 2.0 (CXP-12)

Type:

Color Camera

Manufacturer:

Basler

Mounting Threads:

1/4-20 (Integrated into Housing)

Image Buffer:

Not Specified
Note: Kit includes a camera, CXP-12 interface card, CXP data cable, 2 heat sinks, an I/O cable, and C-Mount Lens adapter (adapter is required to attach lens)
Camera Family: boost
Model Number: boA4112-68cc
Imaging Sensor: Sony IMX253
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1.1"
Resolution (MegaPixels): 12.30
Pixels (H x V): 4,096 x 3,000
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 14.13 x 10.35
Frame Rate (fps): 68.00
Pixel Depth: 8 bit
Exposure Time: Programmable via camera API, hardware trigger
Connector: CoaXPress, Micro-BNC
Power Supply: Power over CoaXPress or via GPIO
Power Consumption (W): 9.6
GPIOs: 1 opto-coupled input, 2 GPIO
Synchronization: Hardware Trigger (GPIO), Software Trigger, or Free-Run
Dimensions (mm): 45 x 80 x 80 (includes connectors and lens mount)
Weight (g): 180
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): Not Specified
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -20 to +80
GPIO Connector Type: 6-pin M7
Machine Vision Standard: CoaXPress 2.0, GenICam
Operating System: Software Driver: Windows

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

