

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #18-723 3-4 DAYS

-

1

+

€4.365,00

ADD TO CART

Qty 1+

€4.365,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Operating Temperature (°C):
+10 to +50

Output Power (mW):
50

Polarization:
100:1 (minimum)

Power Stability (%):
<1

Spatial Mode:

TEM₀₀
Wavelength (nm): 633.00 +0.3/-0.7
Mode Quality, M²: ≤1.3
Warm-Up Time (minutes): <5
Pointing Stability (μrad/°C): <5
Beam Diameter Tolerance (mm): ±0.1
Pointing Stability (μrad): <30
RMS Noise: ≤0.05% (20Hz to 20MHz)
Beam Diameter (mm): 0.5
Spectral Line Width (MHz): 150
Manufacturer: Coherent®
Output Type: Free Space
Type of Laser: Diode
Beam Divergence (mrad): Full-Angle: <2.5
Laser Class - CDRH: IIIb
Color: Red
Model Number: 1448283
Peak-to-Peak Noise: <0.5% (20Hz to 20kHz)
Spectral Line Width (pm): 0.3 (maximum)

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View