

Coherent® OBIS™ 1333336 | 980nm LX 150mW Laser

See More by [Coherent®](#)



Stock #12-359 3-4 DAYS

- 1 +

€3.700,00

ADD TO CART

Qty 1+

€3.700,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
10 to 50

Output Power (mW):
150

Polarization:

100:1
Power Stability (%) : <2
Spatial Mode : TEM ₀₀
Wavelength (nm) : 980.00 ±10
Mode Quality, M² : ≤1.3
Power Supply : Power Supply Required and Sold Separately. USA: #87-473 Europe: #87-473 Japan: #87-473 Korea: #87-473 China: #87-473
Warm-Up Time (minutes) : <5
Pointing Stability (μrad/°C) : <5
Modulation Frequency (MHz) : Max Digital: 150
Modulation Frequency (kHz) : Max Analog: 500
Beam Diameter Tolerance (mm) : ±0.1
Pointing Stability (μrad) : <30
RMS Noise : ≤0.05% (20Hz to 20MHz)
Beam Diameter (mm) : 0.7
Manufacturer : Coherent®
Output Type : Free Space
Type of Laser : Diode
Beam Divergence (mrad) : Full-Angle: ≤2.8
Laser Class - CDRH : IIIB
Color : Infrared
Model Number : 1333336

Regulatory Compliance

RoHS 2015 : Exempt
Reach 224 : Contains SVHC(s)
Certificate of Conformance : View