

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

Conerent® PowerMax USB PM30 Measurement System 1174257 | 350W

See More by [Coherent®](#)



Stock #12-410 [CONTACT US](#)



1



€1.905,00

ADD TO CART

Qty 1+

€1.905,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Active Area Diameter (mm):

19

Model Number:

PM30

Coherent Part Number: 1174257

Type:

Meterless

Type of Sensor: Thermopile
Length of Cable (m): 2.5
Computer Interface: USB
Calibration Uncertainty (%): ±2
Calibration Wavelength (nm): 10600
Long Pulse Joule Mode Range (J): 0.5 - 50
Spectral Compensation Accuracy (%): ±1.5
Maximum Intermittent Power, <5min (W): 50 (air-cooled)
Cooling Method: Air
Maximum Incident Power Density (kW/cm²): 6
Power Range: 10mW - 30W
Maximum Incident Energy Density (J/cm²): 0.6 @ 1064nm, 10ns
Wavelength Range (nm): 190 - 11000
Wavelength Range (µm): 0.19 - 11

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View