

Coherent® OBIS™ 1313871 | 980nm LX 100mW Laser

See More by [Coherent®](#)



Stock #12-358 3-4 DAYS

- 1 +

€2.720,00

ADD TO CART

Qty 1+

€2.720,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
10 to 50

Output Power (mW):
100

Polarization:

100:1
Power Stability (%): <2
Spatial Mode: TEM ₀₀
Wavelength (nm): 980.00 ±10
Mode Quality, M²: ≤1.3
Power Supply: Power Supply Required and Sold Separately. USA: #87-473 Europe: #87-473 Japan: #87-473 Korea: #87-473 China: #87-473
Warm-Up Time (minutes): <5
Pointing Stability (μrad/°C): <5
Modulation Frequency (MHz): Max Digital: 150
Modulation Frequency (kHz): Max Analog: 500
Beam Diameter Tolerance (mm): ±0.1
Pointing Stability (μrad): <30
RMS Noise: ≤0.05% (20Hz to 20MHz)
Beam Diameter (mm): 0.7
Manufacturer: Coherent®
Output Type: Free Space
Type of Laser: Diode
Beam Divergence (mrad): Full-Angle: ≤2.8
Laser Class - CDRH: IIIb
Color: Infrared
Model Number: 1313871

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View