

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

High Resolution Microscopy Star Target



High Resolution Mcroscopy Star Target, #37-538

Stock #37-538 3-4 DAYS



1



€1.050,00

ADD TO CART

Qty 1-4

€1.050,00

Qty 5+

€997,60

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
10 x 10 x 1

Substrate:
[Fused Silica](#) w/Chrome deposit

Optical Density OD (Average):
OD>7 @ 400nm, 6 @ 550nm, 4.5 @ 750nm, 3.6 @ 1000nm

Construction: Stainless Steel, 75 x25 x 1.5mm, microscope slide format
Pattern: 1 central Siemens star with 36 segment pairs, 8mm diameter
Spectral Range: 200 - 2000nm
Pattern Tolerance: 100nm/cm = 10 ⁻⁵

Regulatory Compliance

Reach 191: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View
