

High Resolution Microscope Checker Board



High Resolution Microscope Checker Board, #37-540

Stock **#37-540** 3-4 DAYS

⊖ 1 ⊕ **€950,00**

ADD TO CART

Qty 1-4

€950,00

Qty 5+

€902,60

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
10 x 10 x 1

Substrate: ☐ [Fused Silica](#) w/Chrome deposit

Optical Density OD (Average):
OD>7 @ 400nm, 6 @ 550nm, 4.5 @ 750nm, 3.6 @ 1000nm

Construction: Stainless Steel, 75 x 25 x 1.5mm, microscope slide format
Pattern: Checkerboard 9.0 x 9.0mm ² of 180 x 180 squares of 50 x 50µm ² size
Spectral Range: 200 - 2000nm
Pattern Tolerance: 100nm/cm = 10 ⁻⁵

Regulatory Compliance

Reach 191: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View