

High Resolution Microscopy Resolution Target



High Resolution Microscopy Resolution Target, #37-539

Stock **#37-539** ☐ In Stock

1 **€1.050,00**

ADD TO CART

Qty 1-4
€1.050,00
Qty 5+
€997,60
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
10 x 10 x 1

Substrate: ☐
[Fused Silica](#) w/Chrome deposit

Optical Density OD (Average):
OD>7 @ 400nm, 6 @ 550nm, 4.5 @ 750nm, 3.6 @ 1000nm

Construction: Stainless Steel, 75 x25 x 1.5mm, microscope slide format
Pattern: Pinholes Diameter: 4µm, 2µm, 1µm, 0.5µm, 0.25µm Line patterns: 59 groups, 7.5 - 3300 lp/mm Line Widths: 66.7µm - 0.152µm
Spectral Range: 200 - 2000nm
Pattern Tolerance: 100nm/cm = 10 ⁻⁵

Regulatory Compliance

Reach 191: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View
